

Instellingen Coolpix 4500 ten behoeve van microfotografie

White balance	Manual
Metering	Matrix
Continuous	Single
Best shot selector	Off
Image adjustment	Normal
Saturation control	+1 Enhanced
Image quality	Fine
Image size	2272 x 1520 (3:2)
Image sharpening	Off
Lens	Normal
Exposure options	Off AE lock
Exposure options	Exp. +/-: 0
Focus options	Af area mode: Off
Focus options	S-AF : Single AF
Focus options	Focus confirmation: On
Zoom options	Digital tele: On
Zoom options	Starting position: Off
Zoom options	Fixed aperture: Off
Auto bracketing	Off
Noise reduction	Off



De resultaten zijn te bekijken op www.ronaldschulte.nl